

Product Test Sheet

Product Name: Erbium-Doped Fiber Amplifier

Product Code: STEDFA-C-PA-35-SM-B (LL-EDFA-PA-C-35-SMF-B)

Serial Number: 25101102

Specification	Unit	Min	Test Value	Max	Remarks
Operating Wavelength	nm	1530	1550	1565	
Optical Input Power	dBm	-35		-25	CW
Output Power Stability	-		P-P: ±0.33% RMS: 0.16%		@ -35dBm input, 60min
Small signal gain coefficient	dB		35.3		@-35dBm input, 95mA
Noise Figure	dB			5	
Polarization dependent Gain	dB			0.3	
Polarization mode Dispersion	ps			0.5	
In /Out port Isolation	dB	35			
Operation Temperature Range	°C	-5		+45	
Operation Humidity Range	%			70	
Fiber Connector		FC/APC			
Input / Output Fiber Type		SMF-28e, Φ3mm×1m			
Power Supply	-	AC 100~240V			E.U Standard
Electrical Power Consumption	W	8			25°C
Dimensions	mm	255(W)×285(D)×115(H)			Bench-Top
Remote Control Port	-	RS232-DB9			
Software Version		Amplifier Controller-V20240219			
Control Mode	-	ACC: Automatic Pump Current Control		Current Tuning Range: 0~300mA	
		APC: Automatic Power Control		Power Tuning Range: 1~15dBm	

*Note:

1. If the input signal is a pulsed laser with a repetition frequency <300kHz, do not use the APC mode, only the ACC mode.
2. Note: ISO 11554-2017

8 Evaluation

8.1 General

The standard deviation, s , from n readings m_i is calculated according to

$$s = \sqrt{\frac{\sum_{i=1}^n (m_i - \bar{m})^2}{n-1}} \quad (3)$$

Where the mean value is

$$\bar{m} = \frac{\sum_{i=1}^n m_i}{n} \quad (4)$$

SIMTRUM China
Telephone: +86 133 2643 0008
Email: info@simtrum.com

SIMTRUM Singapore
Telephone: +65 6996 0391
Email: info@simtrum.com




8.3 Power stability of cw lasers


Calculate the mean value of the power, $\bar{P}$, and the respective standard deviation, s , for the appropriate stability time domain (short-term, medium-short-term, medium-term and long-term) according to the specifications given in 7.3.

Power stability is given as the relative power fluctuation, ΔP , in the corresponding stability time domain calculated from Formula (9):

$$\Delta P = \frac{2s}{\bar{P}} \quad (9)$$



Optical Spectrum of Amplified 1550.12nm signal
(-35dBm input power @95mA current)




Output Power vs. Pump Current Curve

SIMTRUM China
Telephone: +86 133 2643 0008
Email: info@simtrum.com

SIMTRUM Singapore
Telephone: +65 6996 0391
Email: info@simtrum.com

SIMTRUM



Power stability test @15dBm, -35dBm input, APC mode (THORLABS S146C)

Date: 2025-10-21